

WARD Flex

Now available in 26 ft or 1000 ft rolls

FOR YOUR CONVENIENCE



Made to the same WARDFlex specifications you know and trust.

Both lengths available in 1/2 inch and 3/4 inch yellow and black CSST.

WARD MFG

117 Gulick Street Blossburg, PA 16917

800.248.1027

www.wardmfg.com

DOWNLOAD THE APP



WARDFlex
JOB SITE
ASSISTANT APP



CONTINUOUS RUN COILS

- No surprises during installation
- WARDFlex tubing is not butt-welded together
- All WARDFlex coils are manufactured in continuous lengths

STEPSAVER DOUBLE-SEALED FITTING

WARDFlex fittings incorporate two independent seats into the sealing of the fitting.

- One metal to metal seat
- One metal to gasket seat as a secondary seat
- Fittings are completely re-usable

HELIUM/ VACUUM TESTING


- 100% of WARDFlex tubing is vacuum tested with helium
- Helium allows for a more stringent test than air testing alone
- WARDFlex tubing is guaranteed 100% leak free

DOUBLE ANNEALED

- All WARDFlex tubing is annealed twice to increase flexibility
- Far more flexible than competitor's product
- Significant reduction in the "spring back" factor



All WARDFlex fittings are compatible with both **Yellow** and **Black** CSST products, ensuring easy installation.



WARDFlex **Stepsaver** design makes installation simple with four easy steps:



1
Cut tubing and remove PE coating to expose a minimum of 4 corrugations.



2
Slide nut over tubing, place retainer ring leaving one corrugation exposed.



3
Slide nut over retainer ring and hand tighten.



4
Tighten with wrenches until nut contacts body.